# High performance & low user cost space-variant CMOS digital camera


#### Information saving

Giotto - mimicking the information saving approach of the human retina - is able to soften the trade-off between image resolution and image dimension.


The sensor has an increasing resolution from the periphery up to the center achieving at the same time a high resolution in the focus point and a broad field of view while limiting the amount of information to be acquired and processed.

The pixels are randomly accessible allowing - if required - the acquisition of smaller regions.

The retina-like configuration gives a more than 30 times reduction in the image dimensions still providing a good perceptual representation thanks to the optimal match between sensor's resolution and retinal resolving power. Such an advantage can be used for a faster frame acquisition or for a lower processing load.



Chip Lay-out



Detail of the central part

## Dynamic response

Giotto retina-like sensor is manufactured in CMOS technology. Each photoreceptor has a non-integrating logarithmic response to lighting variations and consequently a wide dynamic range and a good quality image under different illumination conditions.



Log-polar image



Regular image

### Optimized images

Giotto retina-like camera has a digital output with a rectangular image in *log-polar* format where each ring of the sensor is mapped into a line of a rectangular grid. The log polar mapping is conformal and any "traditional" local processing can be used without modifications (e.g. edge detection, filtering etc.). A simple remapping through a look-up table is sufficient to convert it into a *regular* image.

At present with about 8,000 photosites the sensor produces a rectangular array of 128x76 pixels with a field of view/max resolution equivalent to about a 360,000 pixels uniform sensor.

#### Giotto is supplied as a system:

- the driving software running under Windows '95, Windows-NT 4.0 and Linux
- the camera, acquiring images up to 100 frames/sec.

When interfaced with the parallel port of a Pentium PC, Giotto system performances are:

- limited by the parallel port speed on the EPP mode max. 50 frames/second
- linked to the processor power of the host machine.

### Potential areas of application

The trade-off between image resolution and image size is a critical issue for applications where bandwidth and/or computing power is limited.

The intrinsic information saving characteristic of Giotto offers a strong potential for high performance/low user cost applications in fields such as:

- **remote surveillance**, where it is possible to connect several cameras and transmit useful images on a single physical support (even a twisted pair)
- **robotics, automation and inspection**, reducing the computational requirements and therefore increasing system performance
- **emergency communications**, where the quality of a line connection is not guaranteed and therefore it is necessary to operate in minimal conditions
- **space applications**, where power consumption and volume of computational devices have an enormous cost
- **videotelephony** where strong image compression is key for reaching at the same time a good image quality and a fast frame rate.

In particular as to videotelephony, Giotto exclusive features can be used for:

- a **high performance videophone on analog lines**. It has been successfully tested in a EU research program by achieving the high resolution and fast frame rate required for communication among deaf people through lip and gesture reading
- a high performance/low cost videophone for corporate use.



#### Giotto Technical features

Sansar

ime (non-integrating)			
logarithmic light intensity to output voltage conversion			
ards the center			
Field of view/max resolution equivalent to a uniform sensor array 600×600 pixel			
Windows95, NT 4.0, UNIX			
Parallel port (EPP). RS485 available on request			
Cylindrical - 5.5 cm diameter x 7 cm length			
12 V DC			

Consorzio Unitek - Via della Crocetta 15 - 16122 Genova - Italy Tel.: + 39 010 846.731 Fax: + 39 010 846.7350 e-mail: giotto@unitek.it - http://www.unitek.it